

# DuPont<sup>™</sup> IntegraTec<sup>™</sup> N 42 - L20N v2

# Pressurized and Submerged Module

## **Key Features**

#### Proven N PVDF Fibers:

- · Improved chemical and abrasion resistance.
- Optimized dimensions to maximize packing density with high solid tolerance.

### Optimized Module Design:

- Unique double ended filtration submerged design with CSII rack
- · Highest packing density with high solid loading tolerance
- · High backwash efficiency with Low energy consumption
- Ease of use operation and in-place maintenance
- · Reduced Capital with less civil & construction cost
- Optimized design to suit large size installations
- High tolerance for algae and organic with inline coagulation

## **Key Applications**

New and retrofit submerged filtration of high solids water in:

- Municipal drinking water.
- · Secondary effluent.
- Desalination RO pre-treatment.

## **Module Specification**

General				
Part number / GMID	12038594			
Mode of Filtration	Out-In Submerged			
Membrane Type	Hollow fiber			
Membrane Material	PVDF (Polyvinylidene Fluoride)			
Nominal Membrane Pore Size	0.04	0.04		
Module Operating Process	Deadend	Deadend		
Other Wetted Module Components	Polyurethane, Polyethylene,	Polyurethane, Polyethylene, Polyamide, EPDM		
Dimensions				
Active Membrane Area	42.1 m <sup>2</sup>	453 ft <sup>2</sup>		
Module Length (Overall) (L)	1,800 mm	70.9 inch		
Module Diameter (D)	119 mm	4.7 inch		
Weight and Volume				
Shipping Weight	12 kg	26 lbs.		
Weight Empty	12 kg	26 lbs.		
Hold-Up Volume Feed (Clean-In-Place = CIP)	Depends on tank size	Depends on tank size		
Hold-Up Volume Filtrate (CIP)	Depends on rack/piping sizes	Depends on rack/piping sizes		







# **Suggested Operating Conditions (pressurized)**

General	Details		
Operating Temperature Range	1 - 40 °C	34 - 104 °F	
Operating pH	6 - 9 <sup>1</sup>		
Cleaning pH	2 - 11 <sup>2</sup>		
Typical Filtration Trans-Membrane Pressure (TMP)	0.1 - 1.4 bar	1.5 - 20 psi	
Typical Backwash TMP	0.3 - 1.4 bar	5 - 20 psi	
Backwash Type	Filtrate backwash with air	Filtrate backwash with air scouring	
Backwash Flux	105 L/(m²h)	62 gfd	
Backwash Flow	4 m³h	17.6 gpm	
Operating Limits (Maximum)			
Rate of Temperature Change	n.a.	n.a.	
Inlet Pressure	5 bar	75 psi	
Rate of Pressure Change	0.5 bar / 7.25 psi (feed side	0.5 bar / 7.25 psi (feed side only) , Higher permitted on filtrate side	
Filtration TMP	1.4 bar	20 psi	
Backwash TMP	1.4 bar	20 psi	
Filtration Flux	120 L/(m²h)	71 gfd	
Filtration Flow	5.1 m³h	22.2 gpm	
Backwash Flux	105 L/(m²h)	62 gfd	
Particle Size	300 µm		
Exposure NaOCl	≤ 1,250,000 ppm x h (at pl	≤ 1,250,000 ppm x h (at pH ≥ 6.5, 40 °C)	
Concentration NaOCl	1,500 ppm		

# **Suggested Operating Conditions (submerged)**

General	Details	
Operating Temperature Range	1 - 40 °C	34 - 104 °F
Operating pH	6 - 9 <sup>1</sup>	
Cleaning pH	2 - 11 <sup>2</sup>	
Typical Filtration Trans-Membrane Pressure (TMP)	0.1 - 0.85 bar	1.5 - 12.5 psi
Typical Backwash TMP	0.3 - 0.85 bar	5 - 12.5 psi
Backwash Type	Filtrate backwash with air scouring	
Backwash Flux	105 L/(m²h)	62 gfd
Backwash Flow	4 m³h	17.6 gpm
Operating Limits (Maximum)		
Rate of Temperature Change	n.a.	n.a.
Inlet Pressure	0.85 bar	123 psi
Rate of Pressure Change	n.a.	n.a.
Filtration TMP	0.85 bar	12.5 psi
Backwash TMP	0.85 bar	12.5 psi
Filtration Flux	102 L/(m²h)	60 gfd
Filtration Flow	4.3 m³h	18.9 gpm
Backwash Flux	105 L/(m²h)	62 gfd
Particle Size	300 µm	
Exposure NaOCl	≤ 1,250,000 ppm x h (at pH ≥ 6.5, 40 °C)	
Concentration NaOCl	1,500 ppm	

<sup>1.</sup> Exposure to chloramines is not recommended in feeds below 6.5 pH.

<sup>2.</sup> Initial flushing of new modules followed by a cleaning cycle is recommended prior to use. Please refer to Memcor technical bulletin "Guidelines for flushing new Memcor® 'N' Series Modules" for further details.

<sup>3.</sup> Please contact your sales representative and request the latest version of the manual

#### **General Information**

- Avoid any abrupt pressure variations during start-up, operation, shutdown, cleaning or other sequences to prevent possible membrane damage. The maximum pressure change allowable is 0.5 bar/s.
- Please refer to the DuPont<sup>™</sup> IntegraTec<sup>™</sup> PVDF-UF Out-In S Series CSII MemRack<sup>™</sup> Assembly & Maintenance Guide (Form No. 45-D04540-en)<sup>3</sup>
- If operating limits and guidelines given in this bulletin are not strictly followed, any warranty will be null and void.

## **Regulatory Note**

- Certified drinking water modules require specific conditioning procedures prior to producing potable water. For operating parameters, please refer to DuPont™ IntegraTec™ PVDF-UF Out-In S Series CSII MemRack™ Operating & Maintenance Guide (Form No. 45-D04541-en). <sup>3</sup>
- Drinking water modules may be subjected to additional regulatory restrictions in some countries. Please check local regulatory guidelines and application status before use.



All information set forth herein is for informational purposes only. This information is general information and may differ from that based on actual conditions. Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other government enactments. The product shown in this literature may not be available for sale and/or available in all geographies where DuPont is represented. The claims made may not have been approved for use in all countries. Please note that physical properties may vary depending on certain conditions and while operating conditions stated in this document are intended to lengthen product lifespan and/or improve product performance, it will ultimately depend on actual circumstances and is in no event a guarantee of achieving any specific results. DUPONT ASSUMES NO OBLIGATION OR LIABILITY FOR THE INFORMATION IN THIS DOCUMENT. References to "DuPont" or the "Company" mean the DuPont legal entity selling the products to Customer unless otherwise expressly noted. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED. No freedom from infringement of any patent or trademark owned by DuPont or others is to be inferred.